

## High-performance Food-grade Compressor Oils at Competitive Prices

NDEROL® Specialty Lubricants, the finished fluid division owned by LANXESS, has formulated a unique, high-quality foodgrade semi-synthetic compressor oil that offers outstanding performance at a competitive price.

Semi-synthetic food grade oils are formulated from synergistic blends of severely hydrotreated, hydrocracked (Group III) base oils to provide a more refined, high-quality product. These are enhanced with premium synthetic esters and proven additive technology, which help to improve viscosity, wear resistance at higher temperatures, and stress levels. Furthermore, this also increases their detergency properties, resulting in clean machinery lubrication.

ANDEROL®'s FG S Series offers some of the most desirable charac-

teristics of a premium, fully synthetic lubricant at a significantly lower price. This makes it the ideal choice for customers looking to take advantage of the benefits afforded from synthetic oils over mineral oils without increasing costs. Compatibility is assured with ANDEROL® S-Series lubricant and there is no need for special precautions when switching from a mineral oil-based lubricant for use



18 LUBESNGREASES.COM JULY 2020

with paints, seals, gaskets and hoses.

Successful field trials have shown the oil life of ISO VG 46 and ISO VG 68 exceeds 6,000 hours and can be as high as 10,000 hours.

The FG S Series has numerous advantages over mineral oils, including:

- Lower cost (total cost of ownership)
- Energy savings of up to 4%
- Synthetic grade protection for expensive equipment
- Superb deposit and sludge control
- · Cleaner machinery conditions
- Excellent thermal and oxidative stability
- Superb lubrication and cooling properties
- Excellent heat transfer properties
- High stability even in extreme conditions
- High-temperature shear stability
- Low volatility for longer life
- Good demulsibility and foaming resistance
- Excellent high/low temperature performance
- Elimination of seasonal oil changes
- Cooler compressors
- · Extended drain intervals
- Extended lifetime (an additional 2,000 hours)

ANDEROL®'s FG S range excels in testing compared with standard mineral oil. (See table.)

In four-ball wear tests used to evaluate the anti-wear properties of a lubricant, the ANDEROL® FG S 46 outperforms standard mineral oil.

The scar diameter left as a result of the test determines the ability of the lubricant to prevent wear. The smaller the scar diameter, the better the protection.

Although a four-ball wear test result of less than 0.5 mm is generally regarded as very good, tests indicate that the ANDEROL® FG S 46 lubricant has a result of 0.35 mm—demonstrat-

Test	Sample	Standard Mineral Oil ISO VG 46	ANDEROL® FG S 46
Four-ball wear ASTM D 4172	Average mm	0.46	0.35
Volatility	Petri @ 100°C % evap. loss	7.8	1.8
Thermal oxidation stability PDSC	PDSC Air 200C Mins	86.7	106

ing a very high film strength.

The volatility of a lubricant defines its evaporative loss characteristics. The more volatile it is, the lower the temperature at which smaller hydrocarbon molecules will be driven off or evaporated. The loss of smaller hydrocarbons from the oil can increase the viscosity, especially at higher temperature application. A more volatile lubricant also means greater flammability. The oil film could break on the cylinder, resulting in wear as well as increased oil consumption.

Tests show that the percentage evaporation loss at 100°C over 22 hours is only 1.8% for ANDEROL® FG S 46 compared with 7.8% for standard mineral oil.

The thermal oxidation stability
PDSC test shows equally impressive
results. High-pressure differential
scanning calorimetry is a thermal
analytical method that allows for a
fast and reliable determination of
the thermal oxidation stability of the
lubricant. The PDSC curve is used to
determine the beginning of oxidative
degradation. The time from the first
exposure to air or oxygen until the
onset of the oxidation is called the
oxidation induction time. The longer it
takes until oxidation occurs, the better
the quality of the product.

Under test conditions of 1-4 mg, 200°C, heat rate 100°C/min., 500 psi oxygen, the ANDEROL® FG S 46 clearly offers much better oxidation stability (106) versus standard mineral oil (87).

Just as the service life of the lubricant is important, so too is its **deposit** control.

ANDEROL® FG S 46 boasts exceptional deposit and sludge control, as well as an extremely low degree of deposit formation versus other products.

A series of petri scale tests were completed to demonstrate its performance and thermal oxidation stability. (Visit https://anderol.com/news/fg-s-series for the full results.)

All sample products were placed in a petri dish, heated to 220°C and monitored.

After eight hours, ANDEROL® FG S 46 was lighter in color than its competitors, indicating its thermal stability. It also displayed no sign of sediment.

Even four hours later, its color was largely unchanged while the others had darkened considerably. After 12 hours, it still did not show any polymer/deposit formation.

## To find out more, visit anderol.com

ANDEROL® is a trademark of LANX-ESS Deutschland GmbH or its affiliates. Registered in many countries in the world.

JULY 2020 LUBESNGREASES.COM 19